



Truss grating to facilitate inspection shall run full length (center to center of support frames)  $\pm 12^{\prime\prime}$  on overhead trusses. Cost of truss grating is included in "Overhead Sign Structure".

Handrail, see OS-A-II-DMS

<sup>N</sup> Standard Aluminum Grating

## SECTION A-A

Grating Tiè-downs

Handrail and walkway shall span a minimum of three brackets between splices and/or gap joints. Place all sign and walkway brackets as close to panel points as practical. Grating and handrail splices placed as needed.

Structure Number	Station	а	b	С	Ls	Walkway Grating and Handrail Lengths
4S090I074L100.3	495+10.00	1'-6"	21'-0"	26'-0"	26′-0"	47'-0"
**4S090I074L104.3						

\*\*See ITS plans for existing plans for relocated sign structure.

└ Dynamic Message Sign Cabinet

Alfred Benesch & Company	
205 North Michigan Avenue, Suite 2400	
Chicago, Illinois 60601	

OS-A-9-DMS

benesch

Walkway and Truss Grating

width dimensions are nominal

and may vary ± 1/2" based on

available standard widths.

Chighteets - Sciencists - Planners - 512-555-5450					
	FILE NAME =	USER NAME = mbecker	DESIGNED - MFB	REVISED -	
			CHECKED - KJN	REVISED -	
	xxxxxx_68620_12_ww2.dgn	PLOT SCALE =	DRAWN - MFB	REVISED -	
		PLOT DATE = 7/16/2012	CHECKED - K.IN	REVISED -	

## STATE OF ILLINOIS **DEPARTMENT OF TRANSPORTATION**

						۲
OVERHEAD SIGN STRUCTURES	F.A.I. RTE.	SECTION	COUNTY	TOTAL SHEETS	SHEET NO.	000
ALTERNATE ALUMINUM WALKWAY DETAILS FOR DMS	74	90-[14R;(14HB-4,14,14HVB)BR]	TAZEWELL	2433	1632	ì
ALILINIATE ALUMINION WALKWAT DETAILS TON DINS			CONTRACT	NO. 6	58620	3
CHEET NO CC12 OF CC32 CHEETC		THE INDICE SEED, AND DROUGET				

Safety Chain

\* Space walkway brackets WF6x5.40 for efficiency and within limits shown:

f = 12" maximum, 4" minimum (End of sign to Q of nearest bracket)

20'-0"

26'-0''

g = 12" maximum, 4" minimum (End of walkway grating to Q of nearest support bracket)

h = 6' - 0'' maximum (£ to £ sign and/or walkway support brackets, WF6x5.40

Maximum DMS weight = 5000 lbs. 4'-2" maximum cabinet depth includes depth of cabinet plus connection to WF6x5.40.

For Section B-B and Grating Splice Details, see Base Sheet OS-A-10-DMS. For Handrail Splice Details, see Base Sheet OS-A-11-DMS.